# Introducing our <u>new</u> Coxo Pens & Activators

## Ultra Smart Endo Ultrasonic Activator



**38kHz frequency** - Cleans the root canal more effectively

Ultra Smart

#### S 20 Sec

**One-piece working tip** – Titanium Alloy

- Has good ultrasonic transmission function
- Autoclavable Small. Safe Mini Tips (25#02 size)

#### Auto frequency adjustment



Built-in ARM processor, can auto adjust the frequency according to the load. Detachable silicone cover

Safer working time limit - Auto stop in 20secs. 5sec beeps Large Battery capacity - Sustainable standby 5 hours Simple - One-key control of power on/off. Light = 660gm

### COXO Professional Dental Manufacturer

## **C-FILL mini Endodontic obturation Pen**



#### **4 Sec Heating time**

**4 Precise working Temps** 150, 180, 200 & 230 °C For ALL Gutta Percha

Double Side Controls & Double Displays







**0800 808 855** 

info@henryschein.co.nz

www.henryschein.co.nz